



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**ZB5AW0B45**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**  
 Tightening Torque: 0.8 Nm  
 Light Module Electrical Consumption: 24V = 18mA; 120/240V = 14mA  
 CE: Yes  
 RoHS: Yes  
 Contact Configuration: 1 N.O./1 N.C.  
 Light Module Supply Voltage: 24Vac/dc

**Specification:**  
 Description: Base, Contact, & Light Module  
 Light Module Type: LED(red)  
 Light Module Voltage: 24Vac/dc  
 Ampere Rating: 10A  
 Contact Material: Silver Alloy  
 Terminal Type: Screw Clamp  
 Utilization Category: AC-15; DC-13  
 Used On: ZB5 Plastic Operators