

C60 Familiarity...

■ It's not by pure chance that Multi 9 devices are renowned throughout the world for their quality. Conforming to standards AS/NZS 4898 (IEC 60898), AS 3947-2 (IEC 60947-2), the C60 opened the path to success by becoming the most sold modular circuit breaker in the world.

[choice]

■ The C60 and C120 share the same electrical auxiliaries:

- Snap on
- Interchangeable
- Fewer references to stock

■ TM Motor Mechanisms control your circuit breaker remotely. The TM can be fitted with the C60/C120 electrical auxiliaries or contactor auxiliaries.



[reliability]

■ Quality in the Merlin Gerin tradition:

- C60: 6kA to 10kA, 1 to 63A
- C120N: 10kA, 63 to 125A
- C120H: 15kA, 10 to 125A

■ Control and protection of circuits against overloads and short circuits.



Continued
simple
installation.



■ The priority is simplifying the installation. The C60/C120 range offers an infinite number of possible combinations that are simple to carry out.

[simplicity]

A Complete line of Protection

[offer]



Vigi modules (AS/NZS 61009, IEC/EN 61009)				
basic circuit-breaker	combined Vigi module	instantaneous sensitivity		
		30 mA	300 mA	500 mA
C60N	Vigi C60	■	■	■
C60H	Vigi C60	■	■	■
C120N	Vigi C120	■	■	■
C120H	Vigi C120	■	■	■

Circuit breakers (AS/NZS 4898, IEC/EN 60898)												
particularity	tripping curves			ratings (A)	number of poles	breaking capacity under 415 V (kA)						
	B	C	D			3	4.5	5	6	7.5	10	15
C60N		■		1...63 440	1, 2, 3, 4	■						
C60H	■	■	■	1...63 440	1, 2, 3, 4	■						
C120N	■	■		63...125 440	1, 2, 3, 4	■						
C120H	■	■		10...125 440	1, 2, 3, 4	■						



...C120 Performance!

[safety]



■ With the C120, you now have a complete and compatible range of miniature circuit breakers up to 125A.



■ Adaptable earth leakage modules. The Vigi module can be attached to the circuit breaker with ease. The combination of MCB/RCD conforms to AS/NZS61009 (IEC/EN61009)

C60 and C120 Circuit Breakers Merlin Gerin



*In the field
of **protection**
we can still amaze you....*