



NRNT.E173076 Switches, Industrial Control

[Page Bottom](#)

Switches, Industrial Control

[See General Information for Switches, Industrial Control](#)

SCHNEIDER ELECTRIC INDUSTRIES S A, DBA TELEMECANIQUE
PO BOX 27446
RALEIGH, NC 27611 USA

E173076

Control relays, Part No. RM84 followed by 87, followed by 0, 1, 2, 3 or 4, followed by 0, 1, 2, 3, 4, 5 or 6, followed by 0, 1, 2, 3, 4 or 5, followed by 0, 1, 2, 3, 4, 5, 6 or 7; Part No. RM84 followed by 87, followed by 3, may be followed by 0, 2 or 5, may be followed by 0, 1 or 9, followed by 1, 2, 4 or 9; Part No. RC87 followed by 610, followed by 0, 1, 2, 3 or 4, followed by 4 or 5, followed by 0; Part No. RC87 followed by 618, followed by 2 or 3, followed by 2 or 6, followed by 2, 4 or 8; Part No. RC87 followed by 619, followed by 2 or 3, followed by 2, followed by 2, 4 or 8; Part No. RE88 followed by 826, followed by 0, 1 or 5, followed by 0, 1, 2, 3, 4 or 5, followed by 3, 4 or 5; Part No. RE88 followed by 865, followed by 1, 2, 3 or 5, followed by 0, 1, 2, 3, 4, 5, 6 or 7, followed by 3, 5 or 6; Part No. RE88 followed by 8, followed by 9, followed by 9, followed by 8, followed by 0, followed by 3; Part No. RM84 followed by 870 or 874, followed by 0, 2, 3 or 5, followed by 0, 1, 2 or 3, followed by 1, 2, 3, 4 or 5.

Part Nos. RM35LM33MW, RM35LV14MW, RM17JC00MW, RM35JA31MW, RM35JA32MW, RM17UAS14, RM17UAS16, RM17UAS15, RM17UBE16, RM17UBE15, RM35UA11MW, RM35UA12MW, RM35UA13MW, RM35HZ21FM, RM35UB330, RM35UB3N30, RM17UB310, RM17TG00, RM17TG20, RM17TT00, RM17TU00, RM17TA00, RM17TE00, RM35TF30, RM35TF30SP01, RM35TM50MW, RM35TM250MW, RM35S0MW, RM35ATL0MW, RM35ATR5MW, RM35ATW5MW, RM35BA10.

Electronic timers, Part No. RE11 followed by LA or LC, followed by MW, BM; Part No. RE11 followed by L or R, followed by A, B, C, H, L or M, followed by B, E, J, M or X, followed by M, W or U, followed by S or U; Part No. RE88 followed by 865 followed by 1 or 3, followed by 0 or 8, followed by 0 or 5.

Industrial control switch, open type safety relay, Type XPS LMR.

[Last Updated](#) on 2007-10-05

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2009 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2009 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

