


| KNOCKOUTS | | | | | | | |
|-----------|-----|-----|------|------|------|------|------|
| SYMBOL | A | B | C | D | E | F | G |
| IN | .50 | .75 | 1.00 | 1.25 | 1.50 | 2.00 | 2.50 |
| MM | 13 | 19 | 25 | 32 | 38 | 51 | 64 |



DUAL DIMENSIONS: INCHES
MILLIMETERS

| CATALOG NUMBER | MAXIMUM SYSTEM VOLTAGE | MAINS AMPERE RATING | SPACES | MAXIMUM NUMBER OF SINGLE POLE CIRCUITS | MAIN WIRE SIZE AWG AL/CU |
|----------------|------------------------|---------------------|--------|--|--------------------------|
| QO12436L200TFT | 120/240VAC 1Ø 3W | 200 | 24 | 36 | #4-250 |
| QO12436M200TFT | | 200 | 24 | 36 | |
| QO140L200G | | 200 | 40 | 40 | |
| QO132M150 | | 150 | 32 | 32 | |
| QO140M200 | | 200 | 40 | 40 | |
| QO140M200C | | 200 | 40 | 40 | |
| QO14060L200G | | 200 | 40 | 60 | |
| QO14060M200 | 200 | 40 | 60 | | |

NOTES:
 UL LISTED - FILE E-6294
 NEUTRALS - INSULATED GROUNDABLE.
 LOAD CENTERS WITH "TFT" IN CATALOG NUMBER SUFFIX INCLUDE
 AN INSTALLED EQUIPMENT GROUND BAR AND FEED THRU LUGS.

QO LOAD CENTERS
 GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE
 INDOOR

SQUARE D
 by **Schneider Electric**

DWG# 3008
 NO.