



KNOCKOUTS					
SYMBOL	A	B	C	D	E
IN	.50	.75	1.00	1.25	1.50
MM	13	19	25	32	38



DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO14-8L125GRB	120/240VAC 1 3W	125	4	8	#14-2/0

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSLULATED GROUNDABLE.

QO LOAD CENTERS
RAINPROOF NEMA TYPE 3R ENCLOSURE - OUTDOOR



DWG# 3136
NO.