




KNOCKOUTS		
SYMBOL	IN	MM
A	.50	13
B	.75	19
C	1.00	25
D	1.25	32
E	1.50	38



QO1DM10020TRBR



QO1DM10030TRBR



QO1DM10050TRBR

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	GENERATOR MAIN	POWER INLET TYPE	RATING	MAXIMUM BRANCH BREAKER	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUIT	MAIN WIRE SIZE AWG CU
QO1DM10020TRBR QO1DM10030TRBR QO1DM10050TRBR	120/240 VAC 1Ø3W	100A	20 A 30 A 50 A	NEMA L14-2 NEMA L14-30P HUBBELL CS6375	20 A 30 A 50 A	20 A	4	8	#8-2

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPATIZED STEEL.
UL LISTED - FINE E-6294
NEUTRALS - INSULATED GROUNDABLE.

QO LOAD CENTERS
RAINPROOF NEMA TYPE 3R ENCLOSURE
OUTDOOR

SQUARE D
by Schneider Electric

DWG# 3449
NO.