







KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



DUAL DIMENSIONS: INCHES  
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM CIRCUITS	MAIN WIRE SIZE AWG AL	MAIN WIRE SIZE AWG CU
HOM2040L125PC	120/240VAC 1PH 3W	125	20	40	#6-2/0	#6-1/0
HOM2040L125PGC		125	20	40	#6-2/0	#6-1/0
HOM1632L125PC		125	16	32	#6-2/0	#6-1/0
HOM2448L125PGC		125	24	48	#6-2/0	#6-1/0
HOM2448M100PC		100	24	48	#6-2/0	#6-1/0
HOM2448M125PC		125	24	48	#6-2/0	#6-1/0

NOTES:  
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPATIZED STEEL.  
UL LISTED - FILE E-6294  
NEUTRALS - INSULATED GROUNDABLE.  
LOAD CENTERS WITH A SUFFIX G INCLUDE A FACTORY INCLUDED EQUIPMENT GROUND BAR.

HOMELINE LOAD CENTERS  
GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE  
INDOOR



by Schneider Electric

DWG# PWFDS-SYRS-0068  
NO.