



KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



HOM2040L125PRB



HOM2040M100PRB

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
HOM2040L125PRB	120/240 VAC	125	20	40	#6-2/0 AL
HOM2040M100PRB	10 3W	100			#6-1 CU

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSULATED GROUNDABLE.
WHEN MOUNTING THESE LOAD CENTERS, ALLOW 1.25/[32] INCHES OF CLEARANCE ON HINGED SIDE FOR THE DOOR TO OPEN.

HOMELINE LOAD CENTERS
RAINPROOF NEMA TYPE 3R ENCLOSURE
SIDE HINGED
OUTDOOR



by Schneider Electric

DWG# PWFDS-SYRS-0071
NO.