



KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM CIRCUITS	MAIN WIRE SIZE AWG AL	MAIN WIRE SIZE AWG CU
HOM3060L225PRB	120/240VAC 1PH 3W	225	30	60	#4-300	#4-250
HOM3060M150PRB		150	30	60	#4-250	#4-250
HOM3060M200PRB		200	30	60	#4-250	#4-250

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSULATED GROUNDABLE.
WHEN MOUNTING THESE LOAD CENTERS, ALLOW 1.25/[32] INCHES OF CLEARANCE ON HINGED SIDE FOR THE DOOR TO OPEN.

HOMELINE LOAD CENTERS
RAINPROOF NEMA TYPE 3R ENCLOSURE
SIDE HINGED
OUTDOOR



by Schneider Electric

DWG# PWFDS-SYRS-0078
NO.