




KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



DUAL DIMENSIONS: INCHES  
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM CIRCUITS	MAIN WIRE SIZE AWG AL	MAIN WIRE SIZE AWG CU
HOM4080L225PRB	120/240VAC 1PH 3W	225	40	80	#4-300	#4-250
HOM4080M200PRB		200	40	80	#4-250	#4-250
HOM4284L225PRB		225	42	84	#4-300	#4-250

NOTES:  
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.  
UL LISTED - FILE E-6294  
NEUTRALS - INSULATED GROUNDABLE.  
WHEN MOUNTING THESE LOAD CENTERS, ALLOW 1.25/[32] INCHES OF CLEARANCE ON HINGED SIDE FOR THE DOOR TO OPEN.

HOMELINE LOAD CENTERS  
RAINFOOF NEMA TYPE 3R ENCLOSURE  
SIDE HINGED  
OUTDOOR

**SQUARE D**  
by **Schneider Electric**  
DWG# PWFDS-SYRS-0079  
NO.