



Brodersen System 2000 interface driver ID:44

Interface Description

Technical Data

Electrical Interface	: RS-485
Types of data	: Bits, Bytes Words and Dwords.
PLC types supported	: Brodersen System 2000 Bitbus modules.
Addressing	: Bit read/write DI DO. Word and DWORD read/write AI AO ZI ZO YI YO. Status, LogControl, LogData and System Event
Supported platforms	: Windows Vista, Windows XP, Windows 2003 Server, Windows 2000
Max. telegram size	: 256 bytes per telegram.
Max. number of nodes	: Support for 255 Nodes (Brodersen modules) per network. Max 4096 networks.
PC hardware requirements	: Brodersen UCB-93 Bitbus card.
PC software requirements	: Brodersen UNICOMIO.EXE