





KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



DUAL DIMENSIONS: INCHES  
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM CIRCUITS	MAIN WIRE SIZE AWG AL	MAIN WIRE SIZE AWG CU
HOM2040M150PTBP	120/240VAC 1PH 3W	150	20	40	#4-250	#4-250
HOM2040M200PC		200	20	40	#4-250	#4-250
HOM1632L225PGC		225	16	32	#4-300	#4-250
HOM2040L225PGC		225	20	40	#4-300	#4-250

NOTES:  
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.  
UL LISTED - FILE E-6294  
NEUTRALS - INSULATED GROUNDABLE.  
LOAD CENTERS WITH A SUFFIX G INCLUDE A FACTORY INCLUDED EQUIPMENT GROUND BAR.  
LOAD CENTER WITH SUFFIX BP STANDS FOR BULK PACKED.

HOMELINE LOAD CENTERS  
GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE  
INDOOR



DWG# PWFDS-SYRS-0073 R1  
NO.