


KNOCKOUTS							
SYMBOLS	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64

CABLE TYPE	QWIK GRIP SPACES CAPABILITY						
	10-3 FLAT	10-3 ROUND	10-2	12-3	12-2	14-3	14-2
W1	X	Y	X	X	X	X	X
W2	Y	X	Y	Y	X	Y	X
W3	X	X	Y	Y	X	Y	X
S1	X	X	X	X	Y	X	Y
S2	X	X	X	X	X	X	Y



HOM2448L125PGC

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBERS	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG	
					AL	CU
HOM2448L125PQGC	120/240 VAC 1Ø 3W	125	24	48	#6-2/0	#6-1/0

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSULATED GROUNDABLE.
LOAD CENTERS WITH "P" IN CATALOG NUMBER INCLUDE EXTENDED NEUTRALS FOR PLUG ON NEUTRAL READY INTERIORS.

HOM2448L125PQGC
HOM QWIK GRIP LOAD CENTER GENERAL PURPOSE
NEMA TYPE 1 ENCLOSURE INDOOR



DWG# PWFDS-SYRS-0144
NO.