


KNOCKOUTS							
SYMBOLS	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64

CABLE TYPE	QWIK GRIP SPACES CAPABILITY						
	10-3 FLAT	10-3 ROUND	10-2	12-3	12-2	14-3	14-2
W1	X	Y	X	X	X	X	X
W2	Y	X	Y	Y	X	Y	X
W3	X	X	Y	Y	X	Y	X
S1	X	X	X	X	Y	X	Y
S2	X	X	X	X	X	X	Y



HOM4080L225PQGC HOM4080M200PQC
HOM4080M200PQCVP HOM4284L225PQGC HOM4284M200PQC

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBERS	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG/KCMIL	
					AL	CU
HOM4080L225PQGC	120/240 VAC 1Ø 3W	225	40	80	#4-300	#4-250
HOM4080M200PQC		200	40	80	#4-250	#4-250
HOM4080M200PQCVP		200	40	80	#4-250	#4-250
HOM4284L225PQGC		225	42	84	#4-300	#4-250
HOM4284M200PQC		200	42	84	#4-300	#4-250

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSULATED GROUNDABLE.

HOMELINE QWIK-GRIP
PLUG-ON NEUTRAL LOAD CENTERS
NEMA TYPE 1 ENCLOSURES
INDOOR



DWG# PWFDS-SYRS-0146
NO.