


DUAL DIMENSIONS: INCHES  
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM CIRCUITS	MAIN WIRE SIZE AWG AL	MAIN WIRE SIZE AWG CU
HOM4080M200PC	120/240VAC 1PH 3W	200	40	80	#4-250	#4-250
HOM4080L225PC		225	40	80	#4-300	#4-250
HOM4080L225PGC		225	40	80	#4-300	#4-250
HOM4284M200PC		200	42	84	#4-250	#4-250
HOM4284M225PC		225	42	84	#4-300	#4-250
HOM4284L225PGC		225	42	84	#4-300	#4-250
HOM4284L225PC		225	42	84	#4-300	#4-250

KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



NOTES:  
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPATIZED STEEL.  
 UL LISTED - FILE E-6294  
 NEUTRALS - INSULATED GROUNDABLE.  
 LOAD CENTERS WITH A SUFFIX "G" INCLUDE A FACTORY-INCLUDED EQUIPMENT GROUND BAR.

HOMELINE LOAD CENTERS  
 GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE  
 INDOOR



DWG# PWFDS-SYRS-0075  
 NO.