



KNOCKOUTS		
SYMBOL	CONDUIT SIZE	
	IN	MM
A	.50	13
B	.75	19
C	1.00	25
D	1.25	32
E	1.50	38
F	2.00	51
G	2.50	64

COMBINATION SERVICE ENTRANCE DEVICES
RAINPROOF NEMA TYPE 3R ENCLOSURE
RINGLESS METER MAIN
SURFACE ONLY

DNCS# 1994
Schneider Electric

AMPERE RATING	FACTORY INSTALLED BYPASS TYPE	SHORT CIRCUIT CURRENT RATING	CATALOG NUMBER	SERIES	SPACES	MAXIMUM NUMBER OF SINGLE POLE HOM CIRCUITS	LINE SIDE PHASE & NEUTRAL LUGS AWG/KCMIL	SERVICE GROUND LUG	FEED THROUGH LUGS PHASE & NEUTRAL AWG/KCMIL
100	HORN	22K	RC816F100CH	M01	8	16	#6-350 CU/AL	#14-2/0 CU #12/2/0 AL	#4-250 CU/AL
125	HORN		RC816F125CH						
150	NONE		RC816F150C						
	HORN		RC816F150CH						
200	NONE	RC816F200C							
	HORN	RC816F200CH							