



KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO330MQ125RB	208Y/120VAC 3Ø 4W	125	30	30	#4-250
QO330MQ150RB		150	30	30	
QO330MQ200RB	240/120VAC 3Ø 4W	200	30	30	
QO342MQ200RB		200	42	42	
QO342MQ225RB	240VAC 3Ø 3W	225	42	42	

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSULATED GROUNDABLE.
LOAD CENTERS WITH "G" IN CATALOG NUMBER INCLUDE A FIELD INSTALLABLE EQUIPMENT GROUND BAR KIT.
WHEN MOUNTING THESE LOAD CENTERS, ALLOW 1.25 INCHES OF CLEARANCE ON HINGED SIDE FOR THE DOOR TO OPEN.

QO LOAD CENTERS
GENERAL PURPOSE NEMA TYPE 3R ENCLOSURE
OUTDOOR



DWG# 3042
NO.