


Note:  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**9001KA41**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Technical Information:

UL File: E78403 CCN NKCR  
 CSA File: LR24590 Class 3211-03  
 CE Marked: Yes  
 RoHS compliant: Yes  
 NEMA / IP Rating: n/a  
 Max. Voltage Rating: 120VAC/100VDC

Specification:

Description:  
 Ampere Rating: 0.5A  
 Contact Configuration: 1 NO - 1 NC  
 Contact Type: Logic Reed (Not Fingersafe)  
 Terminal Type: Screw Clamp