

Panel Thickness	Number
E dim.	of
inches (mm)	Gasket
1/16 (1.6)	4
1/8 (3.2)	3
3/16 (4.8)	2
1/4 (6.4)	1





Note:

Drawings Not To Scale
Drawings Subject to Change Without Notice
Dimensions are inches next to [Millimeters]

Part No.:

9001KR25R



Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information: Description: Ring Nut Material:

UL File: E78403 CCN N
CSA File: LR24590 Class
CE Marked: Yes
RoHS: Yes
NEMA / IP Rating: NEMA 1/2/3/3R
Key Number: n/a
Key Removal: n/a
Light Module Supply Voltage: not applicable
Light Module Type: not applicable
Number of Operators: 1 E78403 CCN NKCR LR24590 Class 3211-03

NEMA 1/2/3/3R/4/6/12/13 Water tight, Dust tight and Oil tight (Indoor/Outdoor), IP66

30mm Push Button Chromium Plated Zinc Non-Illuminated

Momentary Screw-On Plastic Mushroom with Set Screw (2.25 Inch/57mm)

No Guard Red

Operator Type:
Operator Action:
Button Type:
Guard Type:
Button/Cap Color:
Lens Type:
Lens Color:
Knob Type: not applicable not applicable not applicable n/a 2

Knob Color: Number of Positions: Specification: