

Panel Thickness	Number		
E dim.	of		
inches (mm)	Gasket		
1/16 (1.6)	4		
1/8 (3.2)	3		
3/16 (4.8)	2		
1/4 (6.4)	1		



 Drawings Not To Scale Drawings Subject to Change Without Notice Dimensions are inches next to [Millimeters] 		9001KS88B			Schneig Pelec
UL File: CSA File: CE Marked: RoHS: NEMA / IP Rating: Key Number: Key Removal: Light Module Supply Voltage: Light Module Type: Number of Operators:	n/a n/a		Description: Ring Nut Material: Operator Type: Operator Action: Button Type: Guard Type: Button/Cap Color: Lens Type: Lens Color: Knob Type: Knob Color: Number of Positions:	30mm Selector Swi Chromium Plated Z Non-Illuminated Maintained n/a n/a not applicable not applicable Standard Knob Black 4	



E dim.



Schneider Electric United States North American Division Boston One Campus 800 Federal Street Andover, MA 01810, USA Phone:+1 8773425173 Email: CCC@us.schneider-electric.com