



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**9080LBA163106**



by **Schneider Electric**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

For Use With:	Copper or Aluminum Wire
Terminal Type:	Lugs
Cover:	9080LB31
Service Class:	C
UL File:	E60616 XCFR2
CSA File:	70361 6228-01
RoHS:	Yes
CE Marked:	Yes
Flammability Rating:	UL94V-0
35mm Track Adapter:	N/A

**Description:**

Ampere Rating:  
 Max. Voltage Rating:  
 Number of Poles:  
 Wire Range - Main:  
 Wire Range - Branch:  
 Short Circuit Current Ratings with Circuit Breakers:  
 Short Circuit Current Ratings with Fuses:

**Specification:**

335A/270A (Cu/Al)  
 600V AC/DC  
 1  
 (1)#6 to 400 AWG/kcmil  
 (6)#14 to #2 AWG  
 Up to 65 kA  
 Up to 200kA