



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

9080LBA264108



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

For Use With: Copper or Aluminum Wire
 Terminal Type: Lugs
 Cover: 9080LB42
 Service Class: C
 UL File: E60616 XCFR2
 CSA File: 70361 6228-01
 RoHS: Yes
 CE Marked: Yes
 Flammability Rating: UL94V-0
 35mm Track Adapter: N/A

Description:
 Ampere Rating: 335A/270A (Cu/Al)
 Max. Voltage Rating: 600V AC/DC
 Number of Poles: 2
 Wire Range - Main: (1)#4 to 600 AWG/kcmil
 Wire Range - Branch: (8)#14 to #2 AWG
 Short Circuit Current Ratings with Circuit Breakers: Up to 65 kA
 Short Circuit Current Ratings with Fuses: Up to 100kA

Specification: