



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**9080LBA362104**



by **Schneider Electric**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

For Use With: Copper or Aluminum Wire  
 Terminal Type: Lugs  
 Cover: 9080LB23  
 Service Class: C  
 UL File: E60616 XCFR2  
 CSA File: 70361 6228-01  
 RoHS: Yes  
 CE Marked: Yes  
 Flammability Rating: UL94V-0  
 35mm Track Adapter: N/A

**Description:**  
 Ampere Rating: 175A/135A (Cu/Al)  
 Max. Voltage Rating: 600V AC/DC  
 Number of Poles: 3  
 Wire Range - Main: (1)#14 to #2/0 AWG  
 Wire Range - Branch: (4)#14 to #4 AWG  
 Short Circuit Current Ratings with Circuit Breakers: Up to 65 kA  
 Short Circuit Current Ratings with Fuses: Up to 100kA

**Specification:**