



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**9080LBA363101**



by **Schneider Electric**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

For Use With:	Copper or Aluminum Wire
Terminal Type:	Lugs
Cover:	9080LB33
Service Class:	C
UL File:	E60616 XCFR2
CSA File:	70361 6228-01
RoHS:	Yes
CE Marked:	Yes
Flammability Rating:	UL94V-0
35mm Track Adapter:	N/A

<b>Description:</b>	
Ampere Rating:	310A/250A (Cu/Al)
Max. Voltage Rating:	600V AC/DC
Number of Poles:	3
Wire Range - Main:	(1)#6 to 350 AWG/kcmil
Wire Range - Branch:	(1)#6 to 350 AWG/kcmil
Short Circuit Current Ratings with Circuit Breakers:	N/A
Short Circuit Current Ratings with Fuses:	N/A

**Specification:**