



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

9080LBC165208



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

For Use With:	Copper Wire Only
Terminal Type:	Lugs
Cover:	9080LB51
Service Class:	C
UL File:	E60616 XCFR2
CSA File:	70361 6228-01
RoHS:	Yes
CE Marked:	Yes
Flammability Rating:	UL94V-0
35mm Track Adapter:	N/A

Description:	
Ampere Rating:	760A (Cu)
Max. Voltage Rating:	600V AC/DC
Number of Poles:	1
Wire Range - Main:	(2)#4 to 500 AWG/kcmil
Wire Range - Branch:	(8)#14 to #2/0 AWG
Short Circuit Current Ratings with Circuit Breakers:	N/A
Short Circuit Current Ratings with Fuses:	Up to 100kA

Specification: