



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

9080LBC362104



by **Schneider Electric**

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone: +1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

For Use With: Copper Wire Only
Terminal Type: Lugs
Cover: 9080LB23
Service Class: C
UL File: E60616 XCFR2
CSA File: 70361 6228-01
RoHS: Yes
CE Marked: Yes
Flammability Rating: UL94V-0
35mm Track Adapter: N/A

Description:

Ampere Rating:
Max. Voltage Rating:
Number of Poles:
Wire Range - Main:
Wire Range - Branch:
Short Circuit Current Ratings with Circuit Breakers:
Short Circuit Current Ratings with Fuses:

Specification:

175A (Cu)
600V AC/DC
3
(1)#14 to #2/0 AWG
(4)#14 to #4 AWG
Up to 65 kA
N/A