



by Schneider Electric

Basic Rack PDU


Overview

The APC by Schneider Electric Basic Rack PDU distributes power to devices in the rack.

Outlets. The Rack PDU has twenty-four (24) NEMA 5-20 outlets.

Power cord. The 10-foot (3.05-meter) power cord terminates with a NEMA L5-20 connector.

AP7530



Specifications

Electrical

Input connector	NEMA L5-20 plug
Output connectors	(24) NEMA 5-20 outlets
Nominal input voltage	120 VAC
Acceptable input voltage	± 10% of nominal voltage
Input frequency	50/60 Hz

Physical

Dimensions (H × W × D)	63.75 x 2.19 x 1.73 in (161.92 x 5.56 x 4.39 cm)
Shipping dimensions (H × W × D)	84.00 x 6.00 x 5.00 in (213.36 x 15.24 x 12.7 cm)
Weight	10 lb (4.54 kg)
Shipping weight	17 lb (7.71 kg)

Environmental

Maximum elevation (above MSL)	
Operating	15,000 ft (4500 m)
Storage	50,000 ft (15 000 m)
Temperature	
Operating	23 to 115° F (–5 to 45° C)
Storage	–13 to 149° F (–25 to 65° C)
Humidity	
Operating	5–95% RH non-condensing
Storage	5–95% RH non-condensing

Compliance

Safety verification	cULus
---------------------	-------

You can find customer support and warranty information on the APC website, www.apc.com.

© 2021 APC by Schneider Electric. All rights reserved.