



### Commercial status

End-of-Sale Notice : OCT 15, 2024

 End-of-Sale Notice

### Main

Range	Acti9
Product or component type	OC contact
Device short name	iOF
Signal contacts composition	1 C/O
[In] rated current	AC-12 6 A at 240 V, AC 50/60 Hz AC-12 3 A at 415 V, AC 50/60 Hz DC-12 2 A at 48 V, DC DC-12 1.5 A at 60 V, DC DC-12 1 A at 130 V, DC DC-12 6 A at 24 V, DC
9 mm pitches	1
Standards	EN/IEC 60947-5-1

### Complementary

[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 KV
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
Height	86 Mm
Width	9 Mm
Depth	73 Mm
Net weight	32 G
Colour	White
Connections - terminals	Screw clamp terminal (bottom) 1 cable(s) 1...4 mm <sup>2</sup> - rigid Screw clamp terminal (bottom) 1 cable(s) 0.5...2.5 mm <sup>2</sup> - flexible Screw clamp terminal (bottom) 2 cable(s) 2.5 mm <sup>2</sup> - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule
Wire stripping length	10 Mm
Tightening torque	1 N.M

### Environment

IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.800 Cm
Package 1 Width	2.000 Cm
Package 1 Length	9.200 Cm
Package 1 Weight	40.000 G
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.500 Cm
Package 2 Width	10.000 Cm
Package 2 Length	27.200 Cm
Package 2 Weight	570.000 G
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30.000 Cm
Package 3 Width	30.000 Cm
Package 3 Length	40.000 Cm
Package 3 Weight	6.350 Kg

## Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**

A9A26924 may be replaced by any of the following products:



### A9A26904

Auxiliary contact, Acti9 A9A, iOF, 1 C/O, 100mA to 6A, 24VAC to 415VAC, 24-130 VDC, bottom connection

Qty 1

Substitution date: |



### A9A26914

Auxiliary contact, Acti9 A9A, iOF, 1 C/O, 2mA to 100mA, 24VAC to 250VAC, 24VDC to 220VDC, bottom connection

Qty 1

Substitution date: |