



## Main

Device application	Distribution
Range	Acti9
Product name	Acti9 iK60
Product or component type	Miniature circuit-breaker
Device short name	iK60N
Poles description	1P
Number of protected poles	1
[In] rated current	6 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability for isolation	Yes conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product certifications	SNI

## Complementary

Network frequency	50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6000 A 100 % conforming to EN/IEC 60898-1 - 230 V AC 50/60 Hz
Limitation class	3 conforming to EN/IEC 60898-1
[Ui] rated insulation voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] rated impulse withstand voltage	4 KV conforming to EN/IEC 60898-1
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	2
Height	85 Mm
Width	18 Mm
Depth	78.5 Mm
Net weight	100 G
Colour	White
Mechanical durability	20000 Cycles
Electrical durability	10000 Cycles

Locking options description	Padlocking device
Connections - terminals	Tunnel type terminal (top or bottom) 1...25 mm <sup>2</sup> rigid Tunnel type terminal (top or bottom) 1...16 mm <sup>2</sup> flexible
Wire stripping length	14 Mm for top or bottom connection
Tightening torque	2 N.M top or bottom
Earth-leakage protection	Without

## Environment

IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	2 conforming to EN/IEC 60898-1
Overvoltage category	III
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 Cm
Package 1 Width	9.4 Cm
Package 1 Length	1.8 Cm
Package 1 Weight	98 G
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	7.8 Cm
Package 2 Width	9.5 Cm
Package 2 Length	21.5 Cm
Package 2 Weight	1244 G
Unit Type of Package 3	S03
Number of Units in Package 3	132
Package 3 Height	30 Cm
Package 3 Width	30 Cm
Package 3 Length	40 Cm
Package 3 Weight	14324 G

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**