



### Main

Range	Acti9
Product or component type	Double OC or fault contact
Device short name	OF and OF or OF and SD
Signal contacts composition	2 C/O
[In] rated current	DC-12 1 A at 130 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC AC-12 3 A at 415 V, AC 50/60 Hz AC-12 6 A at 240 V, AC 50/60 Hz
9 mm pitches	1

### Complementary

Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	NO
Height	90 Mm
Width	9 Mm
Depth	73.5 Mm
Net weight	38 G
Colour	White
Connections - terminals	Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm <sup>2</sup> - flexible Screw clamp terminal (top and bottom) 1 cable(s) 0.5...2.5 mm <sup>2</sup> - rigid Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule
Wire stripping length	9 Mm
Tightening torque	1 N.M

### Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASTA[RETURN]ASEFA[RETURN]LCIE[RETURN]KEMA
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 Cm
Package 1 Width	8 Cm
Package 1 Length	9.2 Cm
Package 1 Weight	46 G
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.7 Cm
Package 2 Width	10 Cm
Package 2 Length	26.5 Cm
Package 2 Weight	609 G
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30 Cm
Package 3 Width	30 Cm
Package 3 Length	40 Cm
Package 3 Weight	5.94 Kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. announced**

## A9N26929 may be replaced by any of the following products:



### A9N26914

Auxiliary contact, Acti9 A9N, OF, 1 C/O, 2mA to 100mA, 24VAC to 250VAC, 24VDC to 220VDC, bottom connection

Qty 1

Substitution date: |



### A9N26917

Auxiliary contact, Acti9 A9N, SD, 1 C/O, 2mA to 100mA, 24VAC to 250VAC, 24VDC to 220VDC, bottom connection

Qty 1

Substitution date: |



### A9N26914

Auxiliary contact, Acti9 A9N, OF, 1 C/O, 2mA to 100mA, 24VAC to 250VAC, 24VDC to 220VDC, bottom connection

Qty 2

Substitution date: |

---



### A9N26909

Auxiliary contact, Acti9 A9N, OF/SD+OF, 2 C/O, 100mA to 6A, 24VAC to 415VAC, 24VDC to 130VDC, top and bottom connection

Qty 1

Substitution date: |

---