

Product data sheet


Characteristics

AK2CA6

Cover for cable duct - Width=60mm

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 23.60 USD



Main

Product or Component Type	Cover
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct 2.36 in (60 mm)
Quantity per Set	Set of 8

Complementary

Color	Blue RAL 5000)
Length	78.74 In (2000 mm)
Width	2.36 In (60 mm)
Material	PVC (polyvinyl chloride)
Net Weight	0.95 Lb(US) (0.43 kg)

Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570267
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.39 In (1.0 cm)
Package 1 Width	3.94 In (10.0 cm)
Package 1 Length	78.74 In (200.0 cm)
Package 1 Weight	16.12 Oz (457.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1120
Package 2 Height	42.52 In (108.0 cm)
Package 2 Width	79.13 In (201.0 cm)
Package 2 Length	47.24 In (120.0 cm)
Package 2 Weight	1316.16 Lb(US) (597.0 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	79.13 In (201.0 cm)
Package 3 Width	4.53 In (11.5 cm)
Package 3 Length	2.56 In (6.5 cm)
Package 3 Weight	8.91 Lb(US) (4.04 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**