

Product data sheet

Characteristics

AK2CD25

Cover for cable duct - Width=25mm

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 13.00 USD



Main

Product or Component Type	Cover
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct 0.98 in (25 mm)
Quantity per Set	Set of 8

Complementary

Color	Gray RAL 7030)
Length	78.74 In (2000 mm)
Width	0.98 In (25 mm)
Material	PVC (polyvinyl chloride)
Net Weight	0.35 Lb(US) (0.16 kg)

Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660

Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570502
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.39 In (1.000 cm)
Package 1 Width	0.98 In (2.500 cm)
Package 1 Length	78.94 In (200.500 cm)
Package 1 Weight	5.54 Oz (157.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	1.18 In (3.000 cm)
Package 2 Width	1.57 In (4.000 cm)
Package 2 Length	79.53 In (202.000 cm)
Package 2 Weight	3.40 Lb(US) (1.544 kg)
Unit Type of Package 3	P2M
Number of Units in Package 3	520
Package 3 Height	17.72 In (45.000 cm)
Package 3 Width	78.74 In (200.000 cm)
Package 3 Length	47.24 In (120.000 cm)
Package 3 Weight	213.05 Lb(US) (96.640 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**