

# Product data sheet

## Characteristics

# AK2CD75

## Cover for cable duct - Width=75mm

Product availability: Stock - Normally stocked in distribution facility

Price\*: 28.40 USD



### Main

Product or Component Type	Cover
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct 2.95 in (75 mm)
Quantity per Set	Set of 8

### Complementary

Color	Gray RAL 7030)
Length	78.74 In (2000 mm)
Width	2.95 In (75 mm)
Material	PVC (polyvinyl chloride)
Net Weight	0.84 Lb(US) (0.38 kg)

### Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0660 VDE 0506 DIN 43659

### Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570557
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	78.74 In (200.0 cm)
Package 1 Width	3.15 In (8.0 cm)
Package 1 Length	1.46 In (3.7 cm)
Package 1 Weight	14.92 Oz (423.0 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	1.38 In (3.5 cm)
Package 2 Width	3.15 In (8.0 cm)
Package 2 Length	78.74 In (200.0 cm)
Package 2 Weight	7.47 Lb(US) (3.39 kg)
Unit Type of Package 3	P2M
Number of Units in Package 3	960
Package 3 Height	47.24 In (120 cm)
Package 3 Width	79.13 In (201 cm)
Package 3 Length	17.72 In (45 cm)
Package 3 Weight	846.58 Lb(US) (384 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**