

# Product data sheet


## Characteristics

# AK2GA35

Cable duct - 55 x 30 mm - without cover - blue

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 39.00 USD



### Main

Product or Component Type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity per Set	Set of 8

### Complementary

Color	Blue RAL 5000)
Fixing Mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	2.17 In (55 mm)
Length	78.74 In (2000 mm)
Width	1.18 In (30 mm)
Net Weight	1.76 Lb(US) (0.8 kg)
Total number of wires	110

### Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660 NF C 68-102

## Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570144
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.35 In (8.5 cm)
Package 1 Width	4.33 In (11.0 cm)
Package 1 Length	78.74 In (200.0 cm)
Package 1 Weight	22.05 Oz (625.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	320
Package 2 Height	30.31 In (77.0 cm)
Package 2 Width	110.24 In (280.0 cm)
Package 2 Length	47.24 In (120.0 cm)
Package 2 Weight	440.92 Lb(US) (200.0 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	4.33 In (11.0 cm)
Package 3 Width	33.46 In (85.0 cm)
Package 3 Length	78.74 In (200.0 cm)
Package 3 Weight	11.02 Lb(US) (5.0 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**