

# Product data sheet

## Characteristics

# AK2GD10075

Cable duct - 75 x 100 mm - without cover - grey

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 68.00 USD



### Main

Product or Component Type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity per Set	Set of 8

### Complementary

Color	Gray RAL 7030)
Fixing Mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 In (75 mm)
Length	78.74 In (2000 mm)
Width	3.94 In (100 mm)
Net Weight	2.65 Lb(US) (1.2 kg)
Total number of wires	550

### Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660

## Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570489
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 In (7.000 cm)
Package 1 Width	3.94 In (10.000 cm)
Package 1 Length	78.74 In (200.000 cm)
Package 1 Weight	2.74 Lb(US) (1.243 kg)
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	5.51 In (14.000 cm)
Package 2 Width	8.07 In (20.500 cm)
Package 2 Length	78.74 In (200.000 cm)
Package 2 Weight	22.91 Lb(US) (10.391 kg)
Unit Type of Package 3	P2M
Number of Units in Package 3	88
Package 3 Height	17.72 In (45.000 cm)
Package 3 Width	78.74 In (200.000 cm)
Package 3 Length	47.24 In (120.000 cm)
Package 3 Weight	274.22 Lb(US) (124.384 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**