

# Product data sheet

## Characteristics

# AK2GD12575

Cable duct - 75 x 125 mm - without cover - grey

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 88.50 USD



### Main

Product or Component Type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity per Set	Set of 8

### Complementary

Color	Gray RAL 7030)
Fixing Mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 In (75 mm)
Length	78.74 In (2000 mm)
Width	4.92 In (125 mm)
Net Weight	3.00 Lb(US) (1.36 kg)
Total number of wires	700

### Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0660 VDE 0506 DIN 43659

## Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570496
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.91 In (15.0 cm)
Package 1 Width	10.24 In (26.0 cm)
Package 1 Length	78.74 In (200.0 cm)
Package 1 Weight	3.31 Lb(US) (1.5 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	72
Package 2 Height	30.31 In (77.0 cm)
Package 2 Width	110.24 In (280.0 cm)
Package 2 Length	47.24 In (120.0 cm)
Package 2 Weight	317.47 Lb(US) (144.0 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	5.91 In (15.0 cm)
Package 3 Width	10.24 In (26.0 cm)
Package 3 Length	78.74 In (200.0 cm)
Package 3 Weight	26.46 Lb(US) (12.0 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**