

Product data sheet


Characteristics

AK2GD5075

Cable duct - 75 x 50 mm - without cover - grey

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 50.00 USD



Main

Product or Component Type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity per Set	Set of 8

Complementary

Color	Gray RAL 7030)
Fixing Mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 In (75 mm)
Length	78.74 In (2000 mm)
Width	1.97 In (50 mm)
Net Weight	1.94 Lb(US) (0.88 kg)
Total number of wires	240

Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	DIN 43659 VDE 0660 VDE 0506

Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
GTIN	3389110570427
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 In (5.0 cm)
Package 1 Width	2.95 In (7.5 cm)
Package 1 Length	78.74 In (200.0 cm)
Package 1 Weight	30.05 Oz (852.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	512
Package 2 Height	45.28 In (115.0 cm)
Package 2 Width	78.94 In (200.5 cm)
Package 2 Length	47.24 In (120.0 cm)
Package 2 Weight	987.67 Lb(US) (448.0 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	4.13 In (10.5 cm)
Package 3 Width	5.51 In (14.0 cm)
Package 3 Length	78.94 In (200.5 cm)
Package 3 Weight	15.43 Lb(US) (7.0 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**