



Visão geral

Apresentação	<p><P>The Network Management Card for Easy UPS On-Line (AP9544) enables secure remote monitoring and control of one Easy UPS Online through the easy-to-use web browser interface, via EcoStruxure™ IT Software or another SNMP-enabled system.</p><p>A 12-month Secure NMC Subscription, that allows the customer to access future firmware updates, is included with the purchase of the card*. Upon expiration of the provided Secure NMC Subscription the purchase of a new Secure NMC Subscription is required to access future firmware updates.</p><p>*The NMC Firmware must be V2.5 or later. Find the latest Firmware in the Software and Firmware section below.</p></p>
Prazo de entrega	Normalmente em stock

Principal

Tipo de produto ou componente	Network interface
Equipamento fornecido	Manual do utilizador Cabo USB

Físico

Altura	4,4 Cm
Largura	5,2 Cm
Profundidade	8,0 Cm
Peso líquido	0,05 Kg
Mounting preference	No preference
Modo de montagem	Not rack-mountable

Conformidade

Normas	CISPR 32 EN 55024 EN 61000-4-2 EN 61000-4-3 EN 61000-4-4 EN 61000-4-5 EN 61000-4-6 EN 61000-4-8 EN 61000-6-2 EN/IEC 62040-2
Certificações de produtos	FCC Classe A[RETURN]ICES-003[RETURN]VCCI Classe A[RETURN]AS/NZS

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ambiental

Temperatura do ar ambiente para operação	-5...45 °C
Altitude de funcionamento	0...10000 ft
Humidade relativa	0...95 %
Temperatura do ar ambiente para armazenamento	-15...65 °C
Altitude de armazenamento	0,00...15240,00 M
Armazenamento Humidade relativa	0...95 %

Comunicações e Gestão

Tipo de rede de comunicação	10/100/1000BASE-T
-----------------------------	-------------------

Unidades de Embalagem

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,600 Cm
Package 1 Width	16,500 Cm
Package 1 Length	23,000 Cm
Package 1 Weight	302,000 G
Unit Type of Package 2	P06
Number of Units in Package 2	44
Package 2 Height	68,000 Cm
Package 2 Width	60,000 Cm
Package 2 Length	80,000 Cm
Package 2 Weight	21,000 Kg

Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACh	Declaração REACh
Diretiva RoHS da UE	Conforme com os requerimentos de excepção
Sem mercúrio	Sim
Regulamento RoHS China	Declaração RoHS China
Informações das isenções RoHS	Sim
Divulgação Ambiental	Perfil Ambiental Do Produto
WEEE	No mercado da União Europeia, o produto tem de ser eliminado de acordo com um sistema de recolha de resíduos específico e nunca terminar num contentor de lixo.

Garantia contratual

Garantia	2 years repair or replace
----------	---------------------------

Product Life Status : **Comercializado**