



### Visão geral

Apresentação	<p>The Network Management Card for Easy UPS 3 Series (AP9547) enables secure remote monitoring and control of one Easy UPS 3S, Easy UPS 3M or Easy UPS 3L through the easy-to-use web browser interface, via EcoStruxure™ IT Software or another SNMP-enabled system.</p> <p>A 12-month Secure NMC Subscription, that allows the customer to access future firmware updates, is included with the purchase of the card. Upon expiration of the provided Secure NMC Subscription the purchase of a new Secure NMC Subscription is required to access future firmware updates.</p>
Prazo de entrega	Normalmente em stock

### Principal

Tipo de produto ou componente	Network interface
Equipamento fornecido	Manual do utilizador Cabo USB

### Físico

Profundidade	8,0 Cm
Peso do produto	0,05 Kg
Mounting preference	No preference
Modo de montagem	Not rack-mountable
Altura	4,4 Cm
Largura	5,2 Cm

### Conformidade

Normas	CISPR 32 EN 55024 EN 61000-4-2 EN 61000-4-3 EN 61000-4-4 EN 61000-4-5 EN 61000-4-6 EN 61000-4-8 EN 61000-6-2 EN/IEC 62040-2
Certificações de produtos	FCC Classe A[RETURN]ICES-003[RETURN]VCCI Classe A[RETURN]AS/NZS

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. \*Prices are indicative

## Ambiental

Temperatura do ar ambiente para operação	-5...45 °C
Altitude de funcionamento	0...10000 ft
Humidade relativa	0...95 %
Temperatura do ar ambiente para armazenamento	-15...65 °C
Altitude de armazenamento	0,0000000000...15240,0000000000 M
Armazenamento Humidade relativa	0...95 %

## Comunicações e Gestão

Tipo de rede de comunicação	10/100/1000BASE-T
-----------------------------	-------------------

## Unidades de Embalagem

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,0 Cm
Package 1 Width	17,0 Cm
Package 1 Length	24 Cm
Package 1 Weight	300 G
Unit Type of Package 2	BB1
Number of Units in Package 2	44
Package 2 Height	49 Cm
Package 2 Width	35 Cm
Package 2 Length	62 Cm
Package 2 Weight	15,08 Kg
Unit Type of Package 3	PAL
Number of Units in Package 3	352
Package 3 Height	114,9 Cm
Package 3 Width	97 Cm
Package 3 Length	97 Cm
Package 3 Weight	125,6 Kg

## Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACH	<a href="#">Declaração REACH</a>
Diretiva RoHS da UE	Conforme com os requerimentos de excepção
Mercury free	Sim
RoHS exemption information	<a href="#">Sim</a>
Regulamento RoHS China	<a href="#">Declaração RoHS China</a>
Divulgação Ambiental	<a href="#">Perfil Ambiental Do Produto</a>
Perfil de Circularidade	<a href="#">Informação Sobre O Fim Da Vida Útil</a>

## Garantia contratual

Garantia	24 meses
----------	----------

Product Life Status : **Comercializado**