

# Product data sheet

## Characteristics

# AP9899

## Cabo de Alimentação, C20 a IEC309 (16 A), 2,5 m



Price\*: 221.54 EUR



### Visão geral

Apresentação	Este cabo ligar uma tomada IEC C19 a um conector IEC 309-16A. Pode ser usado como meio de introduzir uma ficha 16A IEC 309 num PDU montado em bastidor com tomadas IEC C19.
Prazo de entrega	Normalmente em stock

### Principal

Input Connection Type	IEC 60320 C20
Comprimento do cabo	2,50 M

### Físico

Cor	Preto
Altura	9,5 Cm
Largura	29,2 Cm
Profundidade	9,5 Cm
Peso líquido	0,5 Kg
Mounting preference	No preference
Modo de montagem	Not rack-mountable

### Entrada

Max line current	16 A
Input current limits	16 A

### Saída

Number of power socket outlets	1 IEC 60309 16 A 2P + E
--------------------------------	-------------------------

### Conformidade

Certificações de produtos	VDE
---------------------------	-----

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. \*Prices are indicative

## Ambiental

Temperatura do ar ambiente para operação	-10...40 °C
Humidade relativa	20...80 %
Altitude de funcionamento	0...10000 ft
Temperatura do ar ambiente para armazenamento	10...30 °C
Armazenamento Humidade relativa	20...80 %
Altitude de armazenamento	0,00...15240,00 M

## Unidades de Embalagem

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10,2 Cm
Package 1 Width	30,5 Cm
Package 1 Length	10,2 Cm
Package 1 Weight	0,609 Kg
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	25,4 Cm
Package 2 Width	32,2 Cm
Package 2 Length	53,2 Cm
Package 2 Weight	6,12 Kg
Unit Type of Package 3	PAL
Number of Units in Package 3	10
Package 3 Height	143,99 Cm
Package 3 Width	100 Cm
Package 3 Length	120 Cm
Package 3 Weight	6,12 Kg

## Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACH	<a href="#">Declarção REACH</a>
Diretiva RoHS da UE	Conforme <a href="#">Declarção RoHS Da EU</a>
Sem chumbo	Sim
Divulgação Ambiental	<a href="#">Perfil Ambiental Do Produto</a>
Perfil de Circularidade	<a href="#">Informação Sobre O Fim Da Vida Útil</a>
WEEE	No mercado da União Europeia, o produto tem de ser eliminado de acordo com um sistema de recolha de resíduos específico e nunca terminar num contentor de lixo.
Take-back	Take-back program available

## Garantia contratual

Garantia	2 anos para reparação ou substituição
----------	---------------------------------------

Product Life Status : **Comercializado**