

AR100

NetShelter WX 13U c/Orifício Roscado, Porta Dianteira Vidrada em Guia de Montagem Vertical, em Preto



Price*: 1001.27 EUR



Visão geral

Apresentação	Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack hinges at the rear allowing for access to the back of the rack during installation and setup or while undergoing maintenance. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top-mounted and caster kit. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 13U Wall mount cabinet, 19 inches maximum mounting depth, 200lb weight-capacity, 19" rack width, ships fully assembled, glass door, 5 year APC warranty.
Prazo de entrega	Normalmente em stock

Principal

Número de unidade de bastidor	13U
Número de cabos	1
Equipamento fornecido	Tecla(S) Manual do utilizador Guia de montagem de parede

Físico

Cor	Preto
Altura	66,3 Cm
Largura	58,4 Cm
Profundidade	63,1 Cm
Peso líquido	42,73 Kg
Mounting preference	No preference
Modo de montagem	Not rack-mountable
Profundidade de montagem máxima	48,26 Cm
Rack width	19"
Marking	16 gauge EIA mounting rail 16 gauge porta da frente 16 gauge post 13 gauge rear door 18 gauge roof 18 gauge side panels
Carga admissível permanente	90,7 Kg estático

Conformidade

Normas	EIA-310E
--------	----------

Unidades de Embalagem

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	83,8 Cm
Package 1 Width	68,6 Cm
Package 1 Length	77,5 Cm
Package 1 Weight	52,16 Kg

Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
REACH sem SVHC	Sim
Diretiva RoHS da UE	Conformidade proativa (Produto fora do âmbito RoHS da UE) Declaração-RoHS da EU
Sem metais pesados tóxicos	Sim
Sem mercúrio	Sim
Informações das isenções RoHS	Sim
Take-back	Take-back program available

Garantia contratual

Garantia	Reparar ou substituir 5 anos
----------	------------------------------

Product Life Status : **Comercializado**