



Visão geral

Apresentação	Ideal for retail, healthcare, and educational facilities, this wall mount rack offers an efficient solution for deploying server and networking equipment for edge computing applications. This rack enclosure is wall mountable, ideal for areas with limited floor space, and is designed specifically for servers and network switches and patch panels. The cabinet's door is reversible and is compatible with APC's Netbotx security upgrade to provide remote access, video surveillance, and environmental monitoring (sold separately). Optional 120V fan tray can be top or bottom mounted (sold separately) Both the top and bottom feature knockouts of 1/2U mounting space for accessories. And several APC Smart-UPS models low-profile provide easy UPS integration and mounting 12U Wall mount-cabinet, mounting depth range of 2.87 to 20.8 inches, 200lb weight capacity, 19" rack width, ships fully assembled, ventilated with accessory integration options, 5 year APC warranty.
Prazo de entrega	Normalmente em stock

Físico

Profundidade de montagem máxima	52,83 Cm
Número de unidade de bastidor	12U
Minimum mounting depth	7,29 Cm
Cor	Preto
Profundidade	60 Cm
Rack width	19"
Altura	62 Cm
Peso net	19,19 Kg
Carga admissível permanente	90,72 Kg estático
Largura	60 Cm

Conformidades

Normas	UL 2416 EIA-310E
--------	---------------------

Unidades de embalagem

Peso da embalagem (Lbs)	23,18 Kg
Pacote 1 Altura	70 Cm
Pacote 1 largura	68,5 Cm
Pacote 1 Comprimento	68,5 Cm

Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACh	Declaração REACh
REACh sem SVHC	Sim
Diretiva RoHS da UE	Conformidade proativa (Produto fora do âmbito RoHS da UE) Declaração-RoHS da EU
Eficiência energética otimizada	Produto eficiente em termos energéticos
Take-back	Take-back program available

Garantia contractual

Garantia

Reparar ou substituir 5 anos

Product Life Status : **Comercializado**