

# AR3104

Armário em Bastidor de Servidor NetShelter  
SX 24U da APC 600mm x 1070mm c/ Lados  
em Preto



Price\*: 2059.62 EUR



## Visão geral

Apresentação	An industry-standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing.
Prazo de entrega	Normalmente em stock

## Principal

Tipo de produto ou componente	Rack enclosure
Número de unidade de bastidor	24U
Equipamento fornecido	Rodízios Portas Tecla(S) Pés de nivelamento Tecto Painéis laterais

## Físico

Altura	119,85 Cm
Largura	60 Cm
Profundidade	107 Cm
Peso líquido	89,09 Kg
Cor	Preto
Mounting preference	No preference
Modo de montagem	Not rack-mountable
Profundidade de montagem máxima	91,49 Cm
Minimum mounting depth	19,1 Cm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge porta da frente 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Carga admissível permanente	1020,6 Kg dinâmico 1360,8 Kg estático

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. \*Prices are indicative

## Conformidade

Normas	UL 2416 UL 60950-1 EIA-310E
--------	-----------------------------------

## Unidades de Embalagem

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	132,2 Cm
Package 1 Width	74,6 Cm
Package 1 Length	115,6 Cm
Package 1 Weight	106,82 Kg

## Sustentabilidade da oferta

Situação da oferta sustentável	Produto Green Premium
Regulamento REACH	<a href="#">Declarção REACH</a>
REACH sem SVHC	Sim
Diretiva RoHS da UE	Conformidade proativa (Produto fora do âmbito RoHS da UE) <a href="#">Declarção-RoHS da EU</a>
Regulamento RoHS China	<a href="#">Declarção RoHS China</a>
Informações das isenções RoHS	<a href="#">Sim</a>
Divulgação Ambiental	<a href="#">Perfil Ambiental Do Produto</a>
Perfil de Circularidade	<a href="#">Informação Sobre O Fim Da Vida Útil</a>
Take-back	Take-back program available

## Garantia contratual

Garantia	Reparar ou substituir 5 anos
----------	------------------------------

Product Life Status : **Comercializado**