

AR3307

Armário NetShelter SX 48U com 600mm de Largura x 1200mm de Profundidade com Lados, em Preto



Visão geral

| | |
|------------------|--|
| Apresentação | An industry-standard server rack ready for medium to high-density environments with height designed to easily fit through standard doorways. A deeper-rack design provides enough rack mounting space for even the deepest devices and still plenty of room for vertically mounting Rack PDUs and cable management. 48U height allows for an additional 6U of rack mounting space maximizing u-space per rack footprint. |
| Prazo de entrega | Normalmente em stock |

Geral

| | |
|-----------------------|--|
| Equipamento fornecido | Peças de ligação Tecla(S) Pés de nivelamento Hardware de montagem Rodas pré-instaladas Painéis laterais |
|-----------------------|--|

Físico

| | |
|---------------------------------|--|
| Profundidade de montagem máxima | 105,99 Cm |
| Número de unidade de bastidor | 48U |
| Minimum mounting depth | 19,1 Cm |
| Marking | 14 gauge EIA mounting rail 16 gauge porta da frente 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels |
| Cor | Preto |
| Profundidade | 120 Cm |
| Rack width | 19" |
| Altura | 225,8 Cm |
| Peso net | 149,55 Kg |
| Carga admissível permanente | 1020,58 Kg dinâmico 1700,97 Kg estático |
| Largura | 60 Cm |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformidades

| | |
|--------|-----------------------------------|
| Normas | UL 2416 UL 60950-1 EIA-310E |
|--------|-----------------------------------|

Unidades de embalagem

| | |
|--------------------------------|-----------|
| Peso da embalagem (Lbs) | 165,45 Kg |
| Pacote 1 Altura | 238,5 Cm |
| Pacote 1 largura | 75,2 Cm |
| Pacote 1 Comprimento | 133,4 Cm |
| Número de unidades no pacote 3 | 1 |

Sustentabilidade da oferta

| | |
|--------------------------------|---|
| Situação da oferta sustentável | Produto Green Premium |
| Regulamento REACH | Declaração REACH |
| REACH sem SVHC | Sim |
| Diretiva RoHS da UE | Conformidade proativa (Produto fora do âmbito RoHS da UE) Declaração-RoHS da EU |
| Sem metais pesados tóxicos | Sim |
| Sem mercúrio | Sim |
| Informações das isenções RoHS | Sim |
| Take-back | Take-back program available |

Garantia contractual

| | |
|----------|------------------------------|
| Garantia | Reparar ou substituir 5 anos |
|----------|------------------------------|

Product Life Status : **Comercializado**