

# Product data sheet

## Characteristics

# AR4018IA

APC NetShelter CX, 18U, Soundproof Server Rack Enclosure, 200V to 240V, Grey and Oak, 1015H x 750W x 1130D mm



### Overview

Presentation	Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments.
Lead time	Usually in Stock

### General

Provided equipment	Casters Key(S) Leveling feet Rack power distribution unit (PDU) Side panels Unpacking sheet
--------------------	--

### Physical

Maximum mounting depth	88.01 Cm
Number of rack unit	18U
Minimum mounting depth	72.01 Cm
Colour	Grey Oak
Depth	113 Cm
Rack width	19"
Height	101.5 Cm
Product weight	131 Kg
Permanent permissible load	828.26 Kg static
Width	75 Cm

### Input

Network frequency	50/60 Hz
Plug standard	IEC 60320 C14
Input voltage	200 V 208 V 230 V 240 V

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Conformance

Product certifications	TAA compliance
Standards	EIA-310D

## Packing Units

Package 1 Weight	157.5 Kg
Package 1 Height	125 Cm
Package 1 width	80 Cm
Package 1 Length	120 Cm
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------

Product Life Status : **Commercialised**