



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]  
 - Inch Dimensions are derived from the metric.

Part No.:  
**ATS48C11Y**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Control Voltage: 24v  
 Logic Input: 4  
 Analog Input: 1 PTC probe  
 Analog Output: 1  
 Logic/Relay Output: 3  
 Communication: Modbus  
 Weight [lb]/[kg]: 18.3/8.3  
 UL File No.: E184727  
 CSA File: 164581  
 Other: IEC/EN 60947-4-2, EMC classes A & B, CE, DNV, C-Tick, GOST, CCC, NOM, SERPRO AND TCF

**Specification:**

Description:  
 Family: Altistart 48  
 Product Line: Soft Starters  
 Application: Constant & Variable Torque  
 Output Ampere Rating: 110A  
 Max. HP Rating 208V: 30  
 Max. HP Rating 230V: 40  
 Max. kW Rating 400V: 55  
 Max. HP Rating 460V: 75  
 Max. HP Rating 575V: 100  
 Enclosure Rating: IP20  
 Frame Size: B