

# Product data sheet

## Characteristics

# AZ5CE010

Cable ends, Linergy TR cable ends, single conductor, red, 1mm<sup>2</sup>, medium size, 5 sets of 200



Product availability: Stock - Normally stocked in distribution facility

Price\*: 0.18 USD



### Main

|                           |   |
|---------------------------|---|
| Range of Product          | Linergy                                   |
| Product or Component Type | Cable end                                 |
| Cable end size            | Medium                                    |
| Standards                 | NF C 63-023                               |
| Type of Packing           | Dispenser pack                            |
| Quantity per Set          | 5 sets of 200                             |
| Cable cross section       | 0.00 In <sup>2</sup> (1 mm <sup>2</sup> ) |

### Complementary

|                        |                           |
|------------------------|---------------------------|
| Cable end type         | Single conductor          |
| Additional information | Without marker tag holder |
| Color                  | Red                       |
| Bezel material         | Halogen-free plastic      |
| Tube material          | Copper ISO 1337           |
| Number of cables       | 1                         |
| AWG Gauge              | AWG 18                    |
| Bezel size             | Ø 3.5 mm                  |
| Tube diameter          | 0.07 In (1.7 mm)          |
| Length                 | 0.55 In (14 mm)           |
| Tube length            | 0.31 In (8 mm)            |
| Net Weight             | 0.36 Lb(US) (0.165 kg)    |

### Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Product Certifications                | UL                         |
| Ambient air temperature for operation | -4...221 °F (-20...105 °C) |

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US1000I22621  |
| Discount Schedule | 000I          |
| GTIN              | 3389110544022 |
| Returnability     | No            |
| Country of origin | US            |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 0.16 In (0.4 cm)     |
| Package 1 Width              | 0.16 In (0.4 cm)     |
| Package 1 Length             | 0.55 In (1.4 cm)     |
| Package 1 Weight             | 0.04 Oz (1 g)        |
| Unit Type of Package 2       | BB1                  |
| Number of Units in Package 2 | 1000                 |
| Package 2 Height             | 5.12 In (13 cm)      |
| Package 2 Width              | 2.76 In (7 cm)       |
| Package 2 Length             | 4.92 In (12.5 cm)    |
| Package 2 Weight             | 35.27 Oz (1000 g)    |
| Unit Type of Package 3       | S04                  |
| Number of Units in Package 3 | 40000                |
| Package 3 Height             | 11.81 In (30 cm)     |
| Package 3 Width              | 15.75 In (40 cm)     |
| Package 3 Length             | 23.62 In (60 cm)     |
| Package 3 Weight             | 88.18 Lb(US) (40 kg) |

## Offer Sustainability

|                             |   |
|-----------------------------|---|
| Sustainable offer status    | Green Premium product   |
| REACH Regulation            |  <a href="#">REACH Declaration</a>             |
| REACH free of SVHC          | Yes   |
| EU RoHS Directive           | Compliant  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free      | Yes   |
| Mercury free                | Yes   |
| China RoHS Regulation       |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information  |  <a href="#">Yes</a>                           |
| Circularity Profile         | No need of specific recycling operations  |
| WEEE                        | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.      |
| PVC free                    | Yes   |
| Halogen content performance | Halogen free plastic parts product  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**