



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.24 USD



Main

Range of Product	Linergy
Product or Component Type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of Packing	Dispenser pack
Quantity per Set	5 sets of 100
Cable cross section	0.002 In ² (1 mm ²)

Complementary

Cable end type	Twin conductor
Additional information	Without marker tag holder
Color	Red
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	2
AWG Gauge	AWG 18
Bezel size	Ø 3.4 x 5.4 mm
Tube diameter	0.09 In (2.25 mm)
Length	0.6 In (15 mm)
Tube length	0.3 In (8 mm)
Net Weight	0.31 Lb(US) (0.14 kg)

Environment

Product Certifications	cCSAus
Ambient Air Temperature for Operation	-4.0000000000...221.0000000000 °F (-20...105 °C)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110515817
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.157 In (0.400 cm)
Package 1 Width	0.157 In (0.400 cm)
Package 1 Length	0.551 In (1.400 cm)
Package 1 Weight	0.007 Oz (0.200 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	500
Package 2 Height	5.157 In (13.100 cm)
Package 2 Width	2.756 In (7.000 cm)
Package 2 Length	4.921 In (12.500 cm)
Package 2 Weight	4.903 Oz (139.000 g)
Unit Type of Package 3	S04
Number of Units in Package 3	20000
Package 3 Height	11.811 In (30.000 cm)
Package 3 Width	15.748 In (40.000 cm)
Package 3 Length	23.622 In (60.000 cm)
Package 3 Weight	14.107 Lb(US) (6.399 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**