

# Product data sheet

## Characteristics

# AZ5DE015

Cable end, Linergy TR cable ends, twin conductor, black, 1.5mm<sup>2</sup>, for insulated cable, medium size, 5 sets of 50



Product availability: Stock - Normally stocked in distribution facility

Price\*: 0.26 USD



### Main

Range of Product	Linergy
Product or Component Type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of Packing	Dispenser pack
Quantity per Set	5 sets of 100
Cable cross section	0.002 In <sup>2</sup> (1.5 mm <sup>2</sup> )

### Complementary

Cable end type	Twin conductor
Additional information	Without marker tag holder
Color	Black
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	2
AWG Gauge	AWG 16
Bezel size	Ø 3.6 x 6.6 mm
Tube diameter	0.10 In (2.5 mm)
Length	0.6 In (15 mm)
Tube length	0.3 In (8 mm)
Net Weight	0.342 Lb(US) (0.155 kg)

### Environment

Product Certifications	cCSAus
Ambient Air Temperature for Operation	-4.000000000...221.000000000 °F (-20...105 °C)

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110515855
Returnability	No
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.197 In (0.500 cm)
Package 1 Width	0.315 In (0.800 cm)
Package 1 Length	0.630 In (1.600 cm)
Package 1 Weight	0.011 Oz (0.300 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	500
Package 2 Height	5.118 In (13.000 cm)
Package 2 Width	2.756 In (7.000 cm)
Package 2 Length	4.921 In (12.500 cm)
Package 2 Weight	5.326 Oz (151.000 g)
Unit Type of Package 3	S04
Number of Units in Package 3	20000
Package 3 Height	11.811 In (30.000 cm)
Package 3 Width	15.748 In (40.000 cm)
Package 3 Length	23.622 In (60.000 cm)
Package 3 Weight	15.794 Lb(US) (7.164 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**