

Product data sheet

Characteristics

AZ5DE025D

Cable end, Lineryg TR cable ends, twin conductor, blue, 2.5mm², for insulated cable, medium size, 5 sets of 50

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.32 USD



Main

| | |
|---------------------------|--|
| Range of Product | Lineryg |
| Product or Component Type | Cable end |
| Cable end size | Medium |
| Standards | DIN 46228-4 |
| Type of Packing | Dispenser pack |
| Quantity per Set | 5 sets of 50 |
| Cable cross section | 0.004 In ² (2.5 mm ²) |

Complementary

| | |
|------------------------|---------------------------|
| Cable end type | Twin conductor |
| Additional information | Without marker tag holder |
| Color | Gray |
| Bezel material | Halogen-free plastic |
| Tube material | Copper ISO 1337 |
| Number of cables | 2 |
| AWG Gauge | 14 AWG |
| Bezel size | Ø 4.2 x 7.8 mm |
| Tube diameter | 0.1 In (3.2 mm) |
| Length | 0.7 In (18.5 mm) |
| Tube length | 0.4 In (10 mm) |
| Product Weight | 0.320 Lb(US) (0.145 kg) |

Environment

| | |
|---------------------------------------|----------------------------|
| Product Certifications | cCSAus |
| Ambient Air Temperature for Operation | -4...221 °F (-20...105 °C) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US1000I22621 |
| Discount Schedule | 000I |
| GTIN | 3389110518924 |
| Returnability | No |
| Country of origin | DE |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 0.157 In (0.400 cm) |
| Package 1 Width | 0.157 In (0.400 cm) |
| Package 1 Length | 0.551 In (1.400 cm) |
| Package weight(Lbs) | 0.011 Oz (0.300 g) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 250 |
| Package 2 Height | 5.118 In (13.000 cm) |
| Package 2 Width | 2.756 In (7.000 cm) |
| Package 2 Length | 4.961 In (12.600 cm) |
| Package 2 Weight | 4.762 Oz (135.000 g) |
| Unit Type of Package 3 | S02 |
| Number of Units in Package 3 | 2500 |
| Package 3 Height | 5.906 In (15.000 cm) |
| Package 3 Width | 11.811 In (30.000 cm) |
| Package 3 Length | 15.748 In (40.000 cm) |
| Package 3 Weight | 3.726 Lb(US) (1.690 kg) |

Environmental data

| | |
|--|---|
| REACH free of SVHC | Yes |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| Sustainable packaging | No |
| Environmental Disclosure | Product Environmental Profile |
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | No, we have minimized the use of plastic in the packaging in compliance with regulations and consider |
| REACH Regulation | Free of Substances of Very High Concern above the threshold ↗ |
| EU RoHS Directive | Compliant ↗ |
| Halogen content performance | Halogen free plastic parts product |
| PVC free | Yes |
| Silicon free | Yes |
| Circularity Profile | End Of Life Information |
| Take-back | No |

Contractual warranty

| | |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|

Product Life Status : **Commercialised**